


# 馬達電纜

## NEBM-S1G15-E- -LE6

料號: 550747

FESTO

適用於伺服馬達EMMS-ST...



## 技術參數

特性	值
電纜屬性	適合於拖鏈
工作電壓範圍 DC	0 ... 72 V
防護等級	IP65
Note on degree of protection	裝配狀態
Ambient temperature with flexible cable installation	-5 ... 70 °C
環境溫度	-30 ... 70 °C
Bending radius, flexible cable installation	>= 70 mm
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, design	有角的
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	10
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	7
Electrical connection 2, occupied pins/wires	6
導線末端	導線末端套圈
電纜結構	7x0,5 已屏蔽
電纜直徑	8 mm
電纜長度	1 ... 25 m
導體的額定截面	0.5 mm <sup>2</sup>
Cable identification	Without inscription label holder
電纜外套顏色	灰色
材料備註	符合 RoHS
電纜護套的材料訊息	TPE-U(PUR)