

塑料氣管 PUN-V0-6X2-GN-C

料號: 561706

FESTO

阻燃劑



技術參數

特性	值
外徑	6 mm
與流量相關的彎曲半徑	24 mm
內徑	2 mm
最小彎曲半徑	7 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 1.6 MPa
操作壓力的完整溫度範圍	-0.95 ... 16 bar
Operating pressure for entire temperature range	-13.775 ... 232 psi
Temperature-dependent operating pressure	-0.095 ... 3 MPa
溫度取決於操作壓力	-0.95 ... 30 bar
Temperature-dependent operating pressure	-13.775 ... 435 psi
操作壓力注意事項	Water: max. 0.6 MPa at max. 50°C For applications with welding spatter: max. 1 MPa at 20°C, max. 0.9 MPa at 40°C, max. 0.7 MPa at 60°C
授權	TÜV
認證核發部門	B 013277 0506 00
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 V-0 (3mm) UL94 V-2 (0,75mm)
PWIS conformity	VDMA24364-B2-L
環境溫度	-35 ... 60 °C
Note on ambient temperature	For unpressurised use up to 90 °C
產品重量視長度而定	0.032 kg/m
氣壓連接	For push-in connector outside diameter 6 mm 用於倒鉤接頭內徑 2 mm 具螺母
顏色	綠色
關於顏色	由於高溫保護導致偏離標準色
肖氏硬度	D 54 +/-3
材料備註	符合 RoHS
Material tubing	TPE-U(PU)