

連接電纜

NEBC-M9W5-K-2-N-LE3

料號: 563711

FESTO



技術參數

特性	值
Cable identification	具配件
產品重量	108 g
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	電纜
Electrical connection 1, connection technology	開放式終端
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	M9x0,5
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	3
Electrical connection 2, type of mounting	Screw lock
工作電壓範圍 DC	0 ... 30 V
在40°C時的可接受電流負載	1.6 A
Note on acceptable current load at 40°C	2.3 A for 0.34 mm ² 3.6 A for 0.49 mm ²
浪湧強度	0.5 kV
電纜長度	2 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, flexible cable installation	>= 75 mm
電纜直徑	5.5 mm
電纜結構	2x0,25+2x0,34+0,49 已屏蔽
導體的額定截面	0.25 mm ² 0.34 mm ² 0.49 mm ²
導線末端	導線末端套圈
防護等級	IP65 IP67
Note on degree of protection	裝配狀態
環境溫度	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	1
耐腐蝕等級 CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	淡灰色
Material housing	PA PBT

特性	值
	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	TPE-U(PUR)