


插入連接件 CRQS-1/4H-5/32-U

料號: 565355
將停止供貨的產品

FESTO

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



技術參數

特性	值
尺寸	標準
額定尺寸	0.118 "
裝配位置	任何
設計	直式結構
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1.4 MPa
操作壓力的完整溫度範圍	-0.95 ... 14 bar
Operating pressure for entire temperature range	-13.775 ... 203 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-]
耐腐蝕等級 CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364 zone III
Food-safe	See Supplementary material information
環境溫度	-20 ... 150 °C
可使用電線	PFAN
氣壓連接, 氣口 1	Push-in sleeve diameter 1/4"
氣壓連接, 氣口 2	用於5/32" 外徑的氣管
Ambient temperature Fahrenheit	-4 ... 302 °F
材料備註	符合 RoHS
Material housing	高合金鋼, 耐腐蝕
Material release ring	高合金鋼, 耐腐蝕
Material of tubing seal	FPM
Material of tube retaining claw	高合金鋼, 耐腐蝕