


電源模組
VMPAL-SP-QS8
料號: 573645

FESTO



技術參數

特性	值
寬度	23.2 mm
長度	107.3 mm
整合功能	with electrical interlinking module
閥島結構	Valve sizes can be mixed
Operating pressure MPa	-0.09 ... 1 MPa
操作壓力	-0.9 ... 10 bar
Pilot pressure MPa	0.3 ... 0.8 MPa
嚮導壓力	3 ... 8 bar
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-5 ... 50 °C
產品重量	50 g
氣壓連接, 氣口 1	For tubing outside diameter 8 mm
材料備註	符合 RoHS
Material supply module	鍛造鋁合金 PA-加強