


# 連接電纜

## NEBV-Z4WA2L-R-E-0.2-N-Z1W2-S1

料號: 8047682

FESTO



### 技術參數

特性	值
Signal status display	黃色 LED
附加功能	保持電流的降低 Protective circuit
Cable identification	Without inscription label holder
連接頻率	50
產品重量	18 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Connection pattern ZC, metric screw
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 1, type of mounting	通過M2中心螺絲安裝在電磁閥上
Electrical connection 2, function	Controller side
Electrical connection 2, design	有角的
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Connection pattern ZB, self-tapping screw
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Electrical connection 2, type of mounting	通過自攻螺絲安裝在電磁閥上
工作電壓範圍 DC	20.4 ... 26.4 V
額定工作電壓 DC	24 V
浪湧強度	2.4 kV
極性保護	雙極
保護性接地	還未上市
電纜長度	0.2 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, flexible cable installation	>= 29 mm
電纜直徑	2.9 mm
電纜直徑公差	± 0,1 mm
電纜結構	2x0,14
導體的額定截面	0.14 mm <sup>2</sup>
防護等級	IP65
Note on degree of protection	裝配狀態
環境溫度	-10 ... 50 °C
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	3 - High corrosion stress

特性	值
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色
Material housing	TPE-U(PU)
外殼顏色	黑色
Material screws	不鏽鋼
Material electrical contact	Copper alloy, tinned
Material insulation	PP