


接頭

NLFA-D-U14-K3.2-PP-P10

料號: 8104287

FESTO



技術參數

特性	值
容器尺寸	10
設計結構	Tubing mounted via clamped connection
設計	直式結構
尺寸	Diameter 8 mm
Fluid connection	UNF1/4-28
Fluid connection 2	For tubing outside diameter 3.2 mm (1/8")
介質	流體介質 氣態介質
Note on the medium	Observe resistance of materials that come into contact with media
Operating pressure for entire temperature range	-0.075 ... 0.6 MPa
操作壓力的完整溫度範圍	-0.75 ... 6 bar
Operating pressure for entire temperature range	-10.875 ... 87 psi
介質溫度	0 ... 50 °C
環境溫度	0 ... 50 °C
儲藏溫度	-20 ... 70 °C
密封原理	硬性
裝配位置	任何
額定鎖緊扭矩	15 Ncm
額定擰緊扭矩公差	± 15 %
產品重量	0.44 g
材料與介質接觸	PP
Material of threaded plug	PA-加強
材料備註	符合 RoHS
Food-safe	See Supplementary material information
PWIS conformity	VDMA24364 zone III
Instructions for use	See application note (available on the Support Portal at festo.com)