


suction gripper kit for robots OVEL-10-H-15-PQ-VM7-UA-C-A-V1V-H3-RA1

料號: 8121043

FESTO



技術參數

特性	值
額定尺寸, 拉伐爾噴嘴	0.95 mm
排放器特性	高度真空
整合功能	Ejector pulse, electrical 流量控制閥 Pressure transmitter 電控開關閥 過濾器 開放式消音器
Accessories included	1x adapter plate 1x distance piece 1x Velcro® roll 1x USB-Stick mit URcap 1x vacuum generator 1x suction cup with connection 2x connecting cable 5x blanking plugs 6x socket head screws
切換元件功能	常開觸點
切換功能	閾值比較器 具有固定遲滯的閾值
閥功能	已關閉
測量方式	壓阻式壓力感測器
Operating pressure MPa	0.2 ... 0.7 MPa
操作壓力	2 ... 7 bar
最大真空度	92 %
類比輸出	0 - 10 V
工作電壓範圍 DC	21.6 ... 26.4 V
線圈的特性參數	24 V DC: 1 W
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
注意: 操作和嚮導介質	潤滑操作不可行
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
環境溫度	0 ... 50 °C
產品重量	300 g
工作電壓範圍, DC 感測器	18 ... 30 V
Pressure measurement range	-10 ... 0 kPa
壓力測量範圍	-1 ... 0 bar
Electrical connection, input, function	Ejector pulse Vacuum generation
Electrical connection, input, connection type	電纜
Electrical connection, input, connection technology	開放式終端
Electrical connection, input, number of pins/wires	2
Electrical connection, input, cable length	5 m
Electrical connection, output, function	Sensor
Electrical connection, output, connection type	電纜
Electrical connection, output, connection technology	開放式終端

特性	值
Electrical connection, output, number of pins/wires	3
Electrical connection, output, cable length	2.5 m
安裝類型	Via through-hole for M6 screw
Robot connection	Universal robots UR3/5/10 (PolyScope CB 3.8.0 or higher) UR UR3e/5e/10e/16e (ab SW5.0.0)
氣壓連接, 氣口 1	For tubing outside diameter 6 mm
真空連接	G1/4
Note on vacuum connection	Optional: 4x G1/8
材料備註	符合 RoHS
Material of connecting plate	鍛造鋁合金
Material seals	HNBR NBR
Material screws	鋼