


接頭組件

DADG-AK-G8-16-100

料號: 8152386

FESTO



技術參數

特性	值
尺寸	16
行程	100 mm
Operating pressure MPa	0.1 ... 0.8 MPa
操作壓力	1 ... 8 bar
Operating pressure	14.5 ... 116 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-10 ... 60 °C
最大緊固扭矩	1.5 Nm
Tightening torque tolerance	± 10 %
最大的緊固扭矩, 氣接口 1	0.7 Nm
產品重量	19.1 g
氣壓連接	M5
Material adapter	環氧樹脂
Material seals	NBR
Material screws	Coated steel