



Power supply plug NECL-S-L12W5-C2-Q10

料號: 8166792

FESTO



技術參數

特性	值
基於標準	EN 61076-2-111
授權	c UL us - Recognized (OL)
認證核發部門	UL E474609
安裝類型	Threaded
Cable outlet	Angled
Note on cable outlet	Can be rotated 72°
產品重量	45.69 g
Electrical connection 1, function	電源
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭
Electrical connection 1, connection technology	M12x1, L-coded to EN 61076-2-111
Electrical connection 1, number of pins/wires	5
Electrical connection 2, connection technology	螺紋介面
工作電壓範圍 DC	0 ... 63 V
額定工作電壓 DC	63 V
在40°C時的可接受電流負載	16 A
浪湧強度	1.5 kV
容許的電纜直徑	8 - 13 mm for electrical connection 1
導體的額定截面	<= 2.5 mm ²
Nominal conductor cross section (AWG)	AWG14
孔截面的注意事項	Max. 1.5 mm ² /AWG16 when using wire end sleeves
防護等級	IP65 IP67
環境溫度	-40 ... 105 °C
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	1 - Low corrosion stress
Material housing	PA
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Gold-plated copper alloy