

## Spare Parts Catalogue

8073100 VTSA-F-CB (Valve terminal) – Series: All

51E-F33GCQP-RC


















46P-B-NSAB-PSPMNGWZQA-JL

**FESTO**

→ [Catalogue](#)

→ [2D/3D view](#)

→ [Spare parts catalogue](#)

8073100 VTSA-F-CB (Valve terminal)							
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order
1	51E CPX-M - Modular electrical terminal, metal interlinking	550212		CPX-M-EPL-EV End plate	1	PC	
2	F33 Fieldbus node for PROFINET IO, 2 x M12, metal design	548755		CPX-FB33 Bus node	1	PC	
3	QP Connecting block with system supply, 7/8", 5-pin	550208		CPX-M-GE-EV-S-7/8-5POL Interlinking block	1	PC	
4	RC CPX pneumatic interface with serial communication to VTSA-CB, with 3 secure zones (PROFIsafe)	8068240		VABA-S6-1-X2-F1-CB Pneumatic interface	1	PC	
5	N Right-hand end 1/2"	539234		VABE-S6-1R-G12 End plate	1	PC	
6	AB Blanking plug	3571		B-1/2 Blanking plug	1	PC	
7	PS Soft start valve (even tension zone, 0 addresses)	8068610		VABV-S6-1Q-G38-CB-T5 Manifold sub-base	1	PC	
8	PM Soft-start valve, with pilot air provision, with exhaust, duct 3/5	8067407		VABF-S6-1-P5A4S1YE-G12-1T5-PA Soft start valve	1	PC	
9	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC	
10	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
11	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	