
















































8073100 VTSA-F-CB (Valve terminal)							
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order
1	50E CPX - Modular electrical terminal	195716		CPX-EPL-EV End plate	1	PC	
2	-"	195718		CPX-ZA-1 Tie rod	1	PC	
3	F36 Fieldbus node for Ethernet/IP or Modbus TCP, 2 x M12	1912451		CPX-FB36 Bus node	1	PC	
4	QP Connecting block with system supply, 7/8", 5-pin	541244		CPX-GE-EV-S-7/8-5POL Interlinking block	1	PC	
5	RB CPX pneumatic interface with serial communication to VTSA-CB, with 3 external power supplies for the zones	8082879		VABA-S6-1-X1-3V-CB Pneumatic interface	1	PC	
6	N Right-hand end 1/2"	539234		VABE-S6-1R-G12 End plate	1	PC	
7	AB Blanking plug	3571		B-1/2 Blanking plug	1	PC	
8	PS Soft start valve (even tension zone, 0 addresses)	8068610		VABV-S6-1Q-G38-CB-T5 Manifold sub-base	1	PC	
9	PM Soft-start valve, with pilot air provision, with exhaust, duct 3/5	8067407		VABF-S6-1-P5A4S1YE-G12-1T5-PA Soft start valve	1	PC	
10	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC	
11	USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone	8104044		VABF-S6-1-P8A7-G12-CB1 Extension module	1	PC	
12	TL Duct separation 1/14	8060483		VABD-S6-1-P8-C Channel separation	1	PC	
13	PS Soft start valve (even tension zone, 0 addresses)	8068610		VABV-S6-1Q-G38-CB-T5 Manifold sub-base	1	PC	
14	PM Soft-start valve, with pilot air provision, with exhaust, duct 3/5	8067407		VABF-S6-1-P5A4S1YE-G12-1T5-PA Soft start valve	1	PC	
15	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC	
16	USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone	8104044		VABF-S6-1-P8A7-G12-CB1 Extension module	1	PC	
17	TL Duct separation 1/14	8060483		VABD-S6-1-P8-C Channel separation	1	PC	
18	PS Soft start valve (even tension zone, 0 addresses)	8068610		VABV-S6-1Q-G38-CB-T5 Manifold sub-base	1	PC	
19	PM Soft-start valve, with pilot air provision, with exhaust, duct 3/5	8067407		VABF-S6-1-P5A4S1YE-G12-1T5-PA Soft start valve	1	PC	
20	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC	
21	TL Duct separation 1/14	8060483		VABD-S6-1-P8-C Channel separation	1	PC	
22	UW Additional supply plate and exhaust plate with address extension (24 addresses), for unsafe voltage zone	8104042		VABF-S6-1-P8A7-G12-CB Extension module	1	PC	

8073100 VTSA-F-CB (Valve terminal) — Series: All

50E-F36GCQP-RB

46P-B-NSAB-
PSPMNGWZQZAUSWYLYQTLSPMNGWZQZAUSWYLYQTLSPMNGWZQZAYQTLUWY
LNGWA-JLJLJL

8073100 VTSA-F-CB (Valve terminal)							
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order
23	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC	
24	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
25	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
26	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
27	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
28	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
29	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
30	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
31	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	