
































[→ Catalogue](#)[→ 2D/3D view](#)[→ Spare parts catalogue](#)

8073100 VTSA-F-CB (Valve terminal)								
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order	
1	51E CPX-M - Modular electrical terminal, metal interlinking	550212		CPX-M-EPL-EV End plate	1	PC		
2	F33 Fieldbus node for PROFINET IO, 2 x M12, metal design	548755		CPX-FB33 Bus node	1	PC		
3	QP Connecting block with system supply, 7/8", 5-pin	550208		CPX-M-GE-EV-S-7/8-5POL Interlinking block	1	PC		
4	RC CPX pneumatic interface with serial communication to VTSA-CB, with 3 secure zones (PROFIsafe)	8068240		VABA-S6-1-X2-F1-CB Pneumatic interface	1	PC		
5	Y Pilot air selector	539238		VABE-S6-1RZ-G-B1 End plate	1	PC		
6	-"-	3569		B-1/4 Blanking plug	1	PC		
7	U Additional supply plate and exhaust plate (0 addresses)	8092506		VABF-S6-1-P1A7-G12-CB Supply plate	1	PC		
8	YB Manifold sub-base for switchable pilot air with second valve position, size 18 mm (2 addresses)	8068913		VABV-S4-2HS-G18-CB-2T5 Manifold sub-base	1	PC		
9	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
10	L Duct separation 14	573191		VABD-S6-1-P7-C Channel separation	1	PC		
11	USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone	8104044		VABF-S6-1-P8A7-G12-CB1 Extension module	1	PC		
12	YB Manifold sub-base for switchable pilot air with second valve position, size 18 mm (2 addresses)	8068913		VABV-S4-2HS-G18-CB-2T5 Manifold sub-base	1	PC		
13	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
14	L Duct separation 14	573191		VABD-S6-1-P7-C Channel separation	1	PC		
15	USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone	8104044		VABF-S6-1-P8A7-G12-CB1 Extension module	1	PC		
16	YB Manifold sub-base for switchable pilot air with second valve position, size 18 mm (2 addresses)	8068913		VABV-S4-2HS-G18-CB-2T5 Manifold sub-base	1	PC		
17	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
18	UW Additional supply plate and exhaust plate with address extension (24 addresses), for unsafe voltage zone	8104042		VABF-S6-1-P8A7-G12-CB Extension module	1	PC		
19	L Duct separation 14	573191		VABD-S6-1-P7-C Channel separation	1	PC		
20	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
21	CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate	8066569		VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve	1	PC		
22	-"-	3568		B-1/8 Blanking plug	1	PC		


































8073100 VTSA-F-CB (Valve terminal) — Series: All

51E-F33GCQP-RC

46P-B-YS-

UYLNGWOGWYBAYQLUSWYLNWOGWYBAYQLUSWYLNWOGWYBAUWYLNWOG

WYQLA-CSJLLCSJLLCSJLLJL

8073100 VTSA-F-CB (Valve terminal)							
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order
23	-"	1205860		AMTE-M-LH-G18 Silencer	1	PC	
24	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
25	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
26	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
27	CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate	8066569		VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve	1	PC	
28	-"	3568		B-1/8 Blanking plug	1	PC	
29	-"	1205860		AMTE-M-LH-G18 Silencer	1	PC	
30	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
31	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
32	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
33	CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate	8066569		VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve	1	PC	
34	-"	3568		B-1/8 Blanking plug	1	PC	
35	-"	1205860		AMTE-M-LH-G18 Silencer	1	PC	
36	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
37	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
38	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
39	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
40	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	