


Solenoid coil VACN-N-R4-1

Part number: 8104527

FESTO



Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Conforms to standard	DESINA
Signal status display	LED
Duty cycle	100%
Insulation material class	F
Insulation material class of enamelled wire	H
Characteristic coil data	24 V DC: 2.7 W
Pollution degree	3
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C...60 °C
Product weight	100 g
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	4
Electrical connection 1, type of mounting	Screw-type lock
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material housing	Polymer
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper