

Disposable tip DHAP-20-TA1-P960S

Part number: 8160282

FESTO



Data sheet

Feature	Value
Volume	20 µl
Size of pack	960
Design	Pipette tip holder for 20...1000 µl disposable tips from Festo
Packaging type	Stack
Bioburden	ATP: $2 \cdot 10^{-12}$ mg/µl Free of BSE/TSE DNA: <math>< 32</math> pg menschliche DNA DNase: $\leq 5 \cdot 10^{-7}$ Kunitz units/µl Endotoxin: ≤ 0.001 EU/ml RNase: $\leq 5 \cdot 10^{-9}$ Kunitz units/µl
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	5 °C...40 °C
Note on storage temperature	Short-term for transport in packaging -25 ... 55 °C
Relative air humidity	10 - 90% Non-condensing
Environmental conditions	Atmospheric pressure 80 ... 106 kPa
Ambient temperature	5 °C...40 °C
Note on materials	RoHS-compliant
Pipette tip material	PP