

Disposable tip DHAP-1000-TA1FS-P960R

Part number: 8160287

FESTO



Data sheet

| Feature | Value |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Volume | 1000 µl |
| Size of pack | 960 |
| Design | Pipette tip holder for 20...1000 µl disposable tips from Festo |
| Packaging type | Rack |
| Filter | Yes |
| Bioburden | ATP: < $2 \cdot 10^{-12}$ mg/µl Free of BSE/TSE DNA: < 32 pg menschliche DNA DNase: $\leq 5 \cdot 10^{-7}$ Kunitz units/µl Endotoxin: ≤ 0.001 EU/ml RNase: $\leq 5 \cdot 10^{-9}$ Kunitz units/µl |
| Sterility | SAL 1E-6, pre-sterilised |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | 5 °C...40 °C |
| Note on storage temperature | Short-term for transport in packaging -25 ... 55 °C |
| Relative air humidity | 10 - 90% Non-condensing |
| Environmental conditions | Atmospheric pressure 80 ... 106 kPa |
| Ambient temperature | 5 °C...40 °C |
| Note on materials | RoHS-compliant |
| Pipette tip material | PP |