

Piston drive DFPK-75-20-S-T32-V4

Part number: 8198978

FESTO



Data sheet

Feature	Value
Size of valve actuator	75
Stroke	20 mm
Mounting position	optional
Position detection	Via mechanical indicator
Control function	Opened via spring force, N/O
Operating pressure	0.5 MPa...1 MPa 5 bar...10 bar 72.5 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C...60 °C
Degree of protection	IP65 IP67
Ambient temperature	0 °C...60 °C
Product weight	2539 g
Pneumatic connection	Female thread G1/8
Note on materials	RoHS-compliant
Material cover	Stainless steel casting
Material seals	FPM
Material housing	Stainless steel casting
Material number housing	1.4408
Material piston rod	High-alloy stainless steel