

# Push-in fitting NPQO-D-G38-Q10-P5

Part number: 8203300

**FESTO**



## Data sheet

Feature	Value
Nominal size	8.3 mm
Tubing insertion depth	20.1 mm
Type of seal on screwed plug	O-ring
Mounting position	optional
Design	Straight design Push-pull principle
Size of pack	5
Operating pressure complete temperature range	-0.09 MPa...2 MPa -0.9 bar...20 bar -13.05 psi...290 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases Carbon dioxide Air Oxygen Nitrogen
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Media temperature	0 °C...120 °C
Ambient temperature	0 °C...120 °C 32 °F...248 °F
Biocompatibility according to standard	ISO 18562
Oxygen suitability according to standard	ASTM G 93 ISO 15001
Maximum impurity level for hydrocarbons	550 MGM
Max. tightening torque	10 Nm
Nominal torque	9 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	24.31 g
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing outside diameter of 10 mm
Colour of release ring	White
Material screwed plug	High-alloy stainless steel

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS-compliant
Material housing	High-alloy stainless steel
Material thread seal	FPM
Material release ring	PVDF
Material o-ring	FPM
Material tubing seal	FPM
Material tubing clamp component	High-alloy stainless steel
Thrust ring material	PVDF