

Gripper finger cap HAMA-GA-B33-100-4-S-40-BU

Part number: 8203482

FESTO



Data sheet

Feature	Value
Size	100
Min. ø to be gripped	80 mm
Max. ø to be gripped	110 mm
Working stroke	30 mm...125 mm
Number of gripper fingers	4
Design	For grippers Form-fitting Frictional locking
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C...60 °C
Product weight	315 g
Colour	Blue
Shore hardness	A 40 +5
Note on materials	RoHS-compliant
Gripper finger material	VMQ (silicone), metal detectable