


Pressure amplifier PBPA-40-16-A

Part number: 8210528

FESTO



Data sheet

Feature	Value
Piston diameter	40 mm
Mounting position	optional
Design	Twin-piston pressure booster
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/8
Output pressure 2	0.4 MPa...1.6 MPa 4 bar...16 bar 58 psi...232 psi
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar 29 psi...145 psi
Inlet pressure 1	2 bar...10 bar 0.2 MPa...1 MPa 29 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:3:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Product weight	1000 g
Type of mounting	with female thread M4
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/8
Note on materials	RoHS-compliant