


Axial kit EAMM-A-C80-19-108C-S5

FESTO

Part number: 8216594



Data sheet

Feature	Value
Nominal length	76.5 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	6500 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100%
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	21 Nm
Product weight	2650 g
Interface code, actuator	C80-19
Interface code, motor in	108C
Note on materials	RoHS-compliant