

Parallel kit EAMM-U-60-C42-6-68C-91-S5

Part number: 8216596

FESTO



Data sheet

Feature	Value
Size	60
Mounting position	optional
Gear unit ratio	1:1
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100%
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	27.6 kgmm ²
Transmittable torque	3 Nm
Product weight	1640 g
Interface code, actuator	C42-6
Interface code, motor in	68C
Note on materials	RoHS-compliant