

Parallel kit EAMM-U-86-C68-16-88C-102-S5

Part number: 8216601

FESTO



Data sheet

Feature	Value
Size	86
Mounting position	optional
Gear unit ratio	1:1
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100%
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	172.8 kgmm ²
Transmittable torque	9.5 Nm
Product weight	4560 g
Interface code, actuator	C68-16
Interface code, motor in	88C
Note on materials	RoHS-compliant