

# Axial kit EAMM-A-C50-10-79CB-S5

Part number: 8230180

FESTO



## Data sheet

Feature	Value
Nominal length	57.7 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100%
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm <sup>2</sup>
Transmittable torque	12.5 Nm
Product weight	890 g
Interface code, actuator	C50-10
Interface code, motor in	79CB
Note on materials	RoHS-compliant