

# Axial kit EAMM-A-C80-19-148CB-S5

Part number: 8230199

FESTO



## Data sheet

Feature	Value
Nominal length	83 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100%
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	128 kgmm <sup>2</sup>
Transmittable torque	60 Nm
Product weight	3440 g
Interface code, actuator	C80-19
Interface code, motor in	148CB
Note on materials	RoHS-compliant