

# Disposable tip DHAP-20-TA1FS-P960R

Part number: 8160285

FESTO



## Data sheet

Feature	Value
Volume	20 µl
Pack size	960
Structural design	Pipette tip holder for 20...1000 µl single-use tips from Festo
Packing type	Rack
Filter	yes
Bioburden	ATP: < $2 \cdot 10^{-12}$ mg/µl BSE / TSE: free DNA: < 32 pg menschliche DNA DNase: $\leq 5 \cdot 10^{-7}$ Kunitz units/µl Endotoxin: $\leq 0.001$ EU/ml RNase: $\leq 5 \cdot 10^{-9}$ Kunitz units/µl
Sterility	SAL 1E-6, pre-sterilized
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	5 °C...40 °C
Note on storage temperature	short-term for transport in packaging -25 ... 55 °C
Relative air humidity	10 - 90% Non-condensing
Ambient conditions	Atmospheric pressure 80 ... 106 kPa
Ambient temperature	5 °C...40 °C
Note on materials	RoHS-compliant
Pipette tip material	PP