

# Coupling EAMC-42-50-8-16

Part number: 8186207

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	16 mm
Size	42
Nominal length	50 mm...50 mm
Mounting position	Any
Max. rotational speed	6000 rpm...6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...-25 °C
Mass moment of inertia	34.8 kgmm <sup>2</sup>
Transferable torque	17 Nm
Product weight	148 g...148 g
Note on materials	RoHS-compliant