

Manifold block VABS-P4-8S-G18

Part number: 8186785

FESTO



Data sheet

Feature	Value
Width	12 mm
Mounting position	Any
Special features	Oxygen-compatible as per DIN EN 1797
Structural design	Connection direction at side
Max. no. of valve positions	1
Operating pressure	0 bar...10 bar
Operating medium	Inert gas Air Oxygen
Information on operating and pilot media	Operation with oil lubrication not possible Maximum particle size 10 µm
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C...80 °C
Temperature of medium	5 °C...50 °C
Ambient temperature	5 °C...50 °C
Product weight	40 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy, anodized