


Axial kit EAMM-A-L48-50GA-G2

Part number: 8188639

FESTO



Data sheet

Feature	Value
Nominal length	42.5 mm...42.5 mm
Mounting position	Any
Max. rotational speed	6000 rpm...6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	39 kgmm ²
Transferable torque	21 Nm
Product weight	415 g...415 g
Interface code, actuator	L48
Interface code, motor in	50GA
Note on materials	RoHS-compliant