

Coupling EAMD-56-56-25-23X27-U

Part number: 8196717

FESTO



Data sheet

Feature	Value
Diameter of holder 1	25 mm
Diameter of holder 2	23 mm
Size	56
Nominal length	56 mm...56 mm
Mounting position	Any
Max. rotational speed	5500 rpm...5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...-25 °C
Mass moment of inertia	172 kgmm ²
Transferable torque	58 Nm
Product weight	459 g...459 g
Note on materials	RoHS-compliant