


Axial kit EAMM-A-S38-60R-G2

Part number: 8197475

FESTO



Data sheet

Feature	Value
Nominal length	49 mm...49 mm
Mounting position	Any
Max. rotational speed	8000 rpm...8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	290 g...290 g
Interface code, actuator	S38
Interface code, motor in	60R
Note on materials	RoHS-compliant