


Axial kit EAMM-A-S48-80P

Part number: 8197480

FESTO



Data sheet

Feature	Value
Nominal length	72 mm...72 mm
Mounting position	Any
Max. rotational speed	6000 rpm...6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	590 g...590 g
Interface code, actuator	S48
Interface code, motor in	80P 80PA 80RA
Note on materials	RoHS-compliant