

Piston actuator DFPK-46-17-S-T32-V4

Part number: 8198976

FESTO



Data sheet

Feature	Value
Size of valve actuator	46
Stroke	17 mm
Mounting position	Any
Position sensing	With mechanical indicator
Control function	Opened by spring force, N/O
Operating pressure	0.5 MPa...1 MPa 5 bar...10 bar 72.5 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C...60 °C
Degree of protection	IP65 IP67
Ambient temperature	0 °C...60 °C
Product weight	1243 g
Pneumatic connection	Internal thread G1/8
Note on materials	RoHS-compliant
Cover material	Cast stainless steel
Seals material	FPM
Housing material	Cast stainless steel
Material number of housing	1.4408
Piston rod material	High-alloy stainless steel