

Piston actuator DFPK-75-20-S-T32-V4

Part number: 8198978

FESTO



Data sheet

| Feature | Value |
|----------------------------|---|
| Size of valve actuator | 75 |
| Stroke | 20 mm |
| Mounting position | Any |
| Position sensing | With mechanical indicator |
| Control function | Opened by spring force, N/O |
| Operating pressure | 0.5 MPa...1 MPa 5 bar...10 bar 72.5 psi...145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -10 °C...60 °C |
| Degree of protection | IP65 IP67 |
| Ambient temperature | 0 °C...60 °C |
| Product weight | 2539 g |
| Pneumatic connection | Internal thread G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Cast stainless steel |
| Seals material | FPM |
| Housing material | Cast stainless steel |
| Material number of housing | 1.4408 |
| Piston rod material | High-alloy stainless steel |