

Coupling EAMC-56-58-25-25-U

Part number: 8203733

FESTO



Data sheet

Feature	Value
Diameter of holder 1	25 mm
Diameter of holder 2	25 mm
Size	56
Nominal length	58 mm...58 mm
Mounting position	Any
Max. rotational speed	5500 rpm...5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...-25 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	75 Nm
Product weight	266 g...266 g
Note on materials	RoHS-compliant