


Guide unit FEN-20-250-GF

Part number: 8204051

FESTO



Data sheet

| Feature | Value |
|-------------------------------------|--|
| Size | 20 |
| Stroke | 250 mm |
| Mounting position | Any |
| Guide | Sliding guide |
| Structural design | Guide |
| Explosion prevention and protection | Observe the information on the certificate |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -20 °C...80 °C |
| Displacement force | 15 N |
| Moving mass | 569 g |
| Product weight | 1173 g |
| Type of mounting | With internal thread |
| Note on materials | RoHS-compliant |
| Material of guide component | High-alloy steel |
| Housing material | Wrought aluminum alloy, anodized |
| Material of yoke plate | Wrought aluminum alloy, anodized |