

Round cylinder DPRA-N-3/4"-4-NGP4-N

Part number: 8217829

FESTO



Data sheet

Feature	Value
Stroke	4 in
Piston diameter	3/4"
Piston rod thread	1/4-28 UNF-2A
Cushioning	No cushioning
Mounting position	Any
Piston rod end	External thread
Structural design	Piston Piston rod Cylinder barrel
Position sensing	None
Protection against torsion/guide	Round piston rod
Operating pressure	9.99 psi...150 psi
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-40 °F...300 °F
Product weight	0.4 lb
Pneumatic connection	1/8 NPT
Note on materials	RoHS-compliant
Seals material	NBR
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel