

Round cylinder DPRA-N-2"-3-UB-N

Part number: 8217887

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 3 in |
| Piston diameter | 2" |
| Piston rod thread | 1/2-20 UNF-2A |
| Cushioning | No cushioning |
| Mounting position | Any |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | None |
| Protection against torsion/guide | Round piston rod |
| Operating pressure | 9.99 psi...150 psi |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | -40 °F...300 °F |
| Product weight | 1.94 lb |
| Pneumatic connection | 1/4 NPT |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Piston rod material | High-alloy stainless steel |
| Material of cylinder barrel | High-alloy stainless steel |