


Axial kit EAMM-A-C42-6-80CA-S5

Part number: 8230175

FESTO



Data sheet

Feature	Value
Nominal length	58 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100 %
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	1140 g
Interface code, actuator	C42-6
Interface code, motor in	89CA
Note on materials	RoHS-compliant