


Axial kit EAMM-A-C80-19-158CA-S5

Part number: 8230201

FESTO



Data sheet

Feature	Value
Nominal length	82 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100 %
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	60 Nm
Product weight	4510 g
Interface code, actuator	C80-19
Interface code, motor in	158CA
Note on materials	RoHS-compliant