

Kabelis

KMP3-25P-16-10


Gaminio numeris: 18625

Classic - nicht für Neukonstruktionen verwenden

Skirstytuvų salai CPV.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	DIN 41652
Cable identification	su priedais
Prijungimo dažnis	50
Produkto svoris	1.303 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, occupied pins/wires	18
Electrical connection 1, type of mounting	2x M3 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	18
Electrical connection 2, occupied pins/wires	18
Nominalus DC įtampos lygis	0 ... 30 V
Nominali darbinė nuolatinė įtampa	24 V
Leistina srovės apkrova prie 40°C	3 A
Atsparumas smūgiams	1 kV
Kabelio ilgis	10 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandyamas pagal užklausimą
Bending radius, fixed cable installation	≥ 45 mm
Bending radius, flexible cable installation	≥ 90 mm
Kabelio skersmuo	8,5 mm
Kabelio skersmens tolerancija	± 0,5 mm
Kabelio struktūra	18x0,34
Nominalus laidininko skerspjuvis	0,34 mm2
Laido galai	Cut off bluntly
Apsaugos klasė	IP65
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 70 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 70 °C
Saugojimo temperatūra	-25 ... 75 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	PA
Material seals	NBR
Material electrical contact	Gold-plated copper alloy