



Variklio kabelis NEBM-S1G15-E-15-Q7-LE6

Gaminio numeris: 5085058

FESTO



Tech. Duomenys

Savybės	Reikšmė
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	10
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
Nominalus DC įtampos lygis	0 ... 72 V
Nominali darbinė nuolatinė įtampa	24 V
Kabelio ilgis	15 m
Kabelio priedas	Suitable for energy chains
Bending radius, flexible cable installation	≥ 80 mm
Kabelio skersmuo	8 mm
Kabelio struktūra	6x0,75 Ekranuotas
Nominalus laidininko skerspjūvis	0,75 mm ²
Laido galai	Laido antgalis
Apsaugos klasė	IP65
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-40 ... 80 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Atsparumo korozijai klasė CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material insulation	PP