

# Variklio kabelis NEBM-M40G15-EH-5-Q11N-R3LEG14

Gaminio numeris: 5251396

FESTO



## Tech. Duomenys

| Savybės  | Reikšmė  |
|--|--|
| Paremtas standartu   | EN 61984   |
| Cable identification                                       | Without inscription label holder   |
| Produkto svoris  | 2,055 kg   |
| Electrical connection 1, function                          | Field device side  |
| Electrical connection 1, design                            | apvalus  |
| Electrical connection 1, connection type                   | Hybrid socket  |
| Electrical connection 1, cable outlet                      | Tiesus   |
| Electrical connection 1, connection technology             | M40x1  |
| Electrical connection 1, number of pins/wires              | 15   |
| Electrical connection 1, occupied pins/wires               | 12   |
| Electrical connection 1, type of mounting                  | Snap-in locking  |
| Electrical connection 2, function                          | Controller side  |
| Electrical connection 2, connection type                   | Plugs and cables   |
| Electrical connection 2, cable outlet                      | Tiesus   |
| Electrical connection 2, connection technology             | RJ45 and open end  |
| Electrical connection 2, number of pins/wires              | 14   |
| Electrical connection 2, occupied pins/wires               | 12   |
| Nominalus DC įtampos lygis                                 | 0 ... 850 V  |
| Nominalus AC įtampos lygis                                 | 0 ... 630 V  |
| Leistina srovės apkrova prie 40°C                          | 31,9 A   |
| Atsparumas smūgiams  | 6 kV   |
| Kabelio ilgis  | 5 m  |
| Kabelio priedas  | Suitable for energy chains   |
| Laido bandymo sąlygos                                      | Bandymas pagal užklausimą  |
| Bending radius, fixed cable installation                   | 65,6 mm  |
| Bending radius, flexible cable installation                | 123 mm   |
| Kabelio skersmuo   | 16,4 mm  |
| Kabelio skersmens tolerancija                              | ± 0,3 mm   |
| Kabelio struktūra  | 4x4+2x1,5+2x0,24+2x2x0,15  |
| Laido galai  | Laido antgalis   |
| Apsaugos klasė   | IP67   |
| Note on degree of protection                               | Priklausomai nuo ryšio bloko   |
| Aplinkos temperatūra                                       | -40 ... 90 °C  |
| Aplinkos temperatūra esant lankščiai kabelių instaliacijai | -25 ... 80 °C  |
| CE ženklas (žr. deklaraciją)                               | atitinka EU reikalavimus žemose įtampose<br>in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity)               | To UK instructions for electrical equipment<br>To UK RoHS instructions           |
| PWIS conformity  | VDMA24364-B2-L   |
| Informacija  | atitinka RoHS<br>Be halogeno   |
| Užterštumo laipsnis  | 3  |
| Atsparumo korozijai klasė CRC                              | 1 - Low corrosion stress   |
| Material cable sheath                                      | TPE-U(PUR)   |
| Kabelio apvalkalo spalva                                   | pilkas   |
| Material insulation  | PP   |