

Kabelis

KMP6-09P-8-5



Gaminio numeris: 531185

Classic - nicht für Neukonstruktionen verwenden

Miniaturiniamas vožtuvams, su Sub-D, 9-kontaktų 8 ritėms.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	DIN 41652
Cable identification	Without inscription label holder
Prijungimo dažnis	50
Produkto svoris	454 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	9
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	9
Electrical connection 2, occupied pins/wires	9
Nominalus DC įtampos lygis	0 ... 30 V
Nominali darbinė nuolatinė įtampa	24 V
Leistina srovės apkrova prie 40°C	2,8 A
Atsparumas smūgiams	1 kV
Kabelio ilgis	5 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandyamas pagal užklausimą
Bending radius, fixed cable installation	≥ 76 mm
Bending radius, flexible cable installation	≥ 114 mm
Kabelio skersmuo	7,6 mm
Kabelio skersmens tolerancija	± 0,25 mm
Kabelio struktūra	8x0,34+1x0,5
Nominalus laidininko skerspjuvis	0,34 mm ² 0,5 mm ²
Laido galai	Cut off bluntly
Apsaugos klasė	IP40
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 70 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 70 °C
Saugojimo temperatūra	-25 ... 75 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	2

Savybės	Reikšmė
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	PBT-sustiprintas
Korpuso spalva	pilkas
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy