


Pajungimo kabelis NEBV-S1W37-KM-5-LE27

Gaminio numeris: 543275

FESTO

Skirstytuvų salų VTSA ir VTSA-F daugiapolinei jungčiai, iki. 22 skirstytuvų rėčių, su Sub-D kištuko lizdu, 27-polių.



Tech. Duomenys

Savybės	Reikšmė
Naudojimo sritis	Only for multi-pin plug connection valve terminal VTSA/VTSA-F
Atitinka standartus	DIN 47100
Cable identification	With inscription label holder
Produkto svoris	1.124 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	37
Electrical connection 1, occupied pins/wires	27
Electrical connection 1, type of mounting	3x M4 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	27
Electrical connection 2, occupied pins/wires	27
Nominalus DC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	2 A
Atsparumas smūgiams	1 kV
Kabelio ilgis	5 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	≥ 44 mm
Bending radius, flexible cable installation	≥ 82 mm
Kabelio skersmuo	10,9 mm
Kabelio struktūra	27x0,34
Nominalus laidininko skerspjūvis	0,34 mm ²
Apsaugos klasė	IP65 NEMA 4
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-5 ... 50 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	PA
Material insulation	PVC