



Pajungimo kabelis NEBB-M12W5-P-10-LE3

Gaminio numeris: 8066681

FESTO



Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	Core colours and connection numbers to EN 60947-5-2 EN 61076-2-101
Cable identification	With inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuvo lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Screw lock with A/F13
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atvirai laidai
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Nominalus DC įtampos lygis	0 ... 250 V
Nominalus AC įtampos lygis	0 ... 250 V
Leistina srovės apkrova prie 40°C	4 A
Atsparumas smūgiams	2,5 kV
Kabelio ilgis	10 m
Kabelio priedas	Statiniam panaudojimui
Laido bandymo sąlygos	Bandyamas pagal užklausimą
Bending radius, fixed cable installation	≥ 12 mm
Kabelio skersmuo	3,8 mm
Kabelio struktūra	3x0,25
Nominalus laidininko skerspjūvis	0,25 mm ²
Laido galai	Sheath removed Cut off bluntly
Apsaugos klasė	IP65 IP68 IP69K
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 70 °C
CE ženklas (žr. deklaraciją)	atitinka EU reikalavimus žemose įtampose in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Švaros klasė	ISO class 4
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	TPE-U(PU)

Savybės	Reikšmė
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulation	PVC