


# Pajungimo kabelis

## NEBC-R3G8-KS-0.2-N-S-R3G8-ET

Gaminio numeris: 8082383

★ Kernprogramm

FESTO



## Tech. Duomenys

Savybės	Reikšmė
Cable identification	Without inscription label holder
Produkto svoris	15 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištukas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	RJ45
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, design	kampinis
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	RJ45
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Nominalus DC įtampos lygis	0 ... 50 V
Leistina srovės apkrova prie 40°C	1,5 A
Atsparumas smūgiams	2,5 kV
Shielding	Taip
Kabelio ilgis	0,2 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	24 mm
Kabelio skersmuo	5 mm
Kabelio struktūra	4 x 2 x 0.16 mm <sup>2</sup>
Nominalus laidininko skerspjuvis	0,16 mm <sup>2</sup>
Apsaugos klasė	IP20
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-20 ... 60 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	2
Atsparumo korozijai klasė CRC	0 - No corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	PVC
Korpuso spalva	pilkas
Material insulation	PVC