



Pajungimo kabelis NEBC-M12W8-E-2-N-B-LE8

Gaminio numeris: 8094476

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61076-2-101
Leidimas	c UL us - Listed (OL)
Skyriaus sertifikatas	UL E474609
Cable identification	Without inscription label holder
Produkto svoris	105 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuvo lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Nominalus DC įtampos lygis	0 ... 30 V
Nominalus AC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	2 A
Atsparumas smūgiams	0,8 kV
Shielding	Ne
Kabelio ilgis	2 m
Kabelio priedas	Suitable for energy chains
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	≥ 30 mm
Bending radius, flexible cable installation	≥ 30 mm
Kabelio skersmuo	6 mm
Kabelio skersmens tolerancija	± 0,2 mm
Kabelio struktūra	8x0,25
Nominalus laidininko skerspjūvis	0,25 mm ²
Laido galai	Sheath removed
Apsaugos klasė	IP65 IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 90 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-25 ... 90 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	Silver-grey

Savybės	Reikšmė
Material housing	TPE-U(PUR)
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Žalvaris
Material insulation	PP