

Plastikiniai vamzdeliai PUN-H-SF-25X4,85-SW-25

Gaminio numeris: 8167917

FESTO



Tech. Duomenys

Savybės	Reikšmė
Išorinis diametras	25 mm
Lenkimo spindulys atitinkantis srautą	130 mm
Vidinis diametras	15,3 mm
Min. lenkimo spindulys	55 mm
Instructions for use	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Darbiis slėgis visam temperatūros diapozonui.	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1,3 MPa
Temperatūros priklausomybė nuo darbinio slėgio	-0,95 ... 13 bar
Temperature-dependent operating pressure	-13,775 ... 188,5 psi
Nuoroda į darbinį slėgį	Water: temperature-dependent operating pressure, see diagram, max. 0.7 MPa at 0 - 60°C
Darbinė terpė	Suslėgto oro kokybė pagal ISO8573-1:2010 [7::-:] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Švaros klasė	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Aplinkos temperatūra	-35 ... 80 °C
Produkto svoris pagal ilgį	0,372 kg/m
Spalva	Juodas
Atramos kietumas	D 54 +/-3
Informacija	atitinka RoHS
Material tubing	TPE-U(PU)