

# Cuplaj EAMD-56-56-25-23X27-U

Numar piesa: 8196717

FESTO



## Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	25 mm
Diametru de montare 2	23 mm
Dimensiune	56
Lungime nominala	56 mm...56 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min...5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...-25 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...-25 °C
Momentul de inertie al masei	172 kgmm <sup>2</sup>
Cuplu transmisibil	58 Nm
Greutate produs	459 g...459 g
Nota privind materialele	Conform RoHS